

JET®


**HIGH TECHNOLOGY AGITATOR
FOR STRATEGICAL PROCESSES**

- **AGITATION FOR INTENSIVE USE AND HARD WORKING ENVIRONMENT: PRESSURE, TEMPERATURE, PRODUCT**
- **EQUIPPED WITH THE MOST ADVANCED SEALING SYSTEMS TECHNOLOGIES**
- **ERGONOMICS FOR FAST MAINTENANCE OPERATIONS**

**Agitator with JET® Type turret,
dedicated to chemical, pharmaceutical
and petrochemical processes**

Up to 180 bars, 200 kW and 300°C

- > **Chemical reaction**
 - > **Heat transfer**
 - > **Crystallization**
 - > **Fermentation**








mixel
agitators

JET®


HIGH TECHNOLOGY AGITATOR
FOR STRATEGICAL PROCESSES

- **Guiding turret** for lateral extraction of sealing box
- Sealing box maintenance **with full tank**
- **Fast dismantling** of the sealing box within less than 4 hours
- **Easy access** to sealing box
- Hydraulic jack for **highly secured dismantling operation**
- **Only one technician** to operate maintenance in safe conditions
- **No need of extra specific tool**

► Sealing system dismantling stages with full or empty tank



- 1st dismantling stage
- 2 Uncoupling of driving shaft
- 3 Uncoupled and blocked driving shaft
- 4 Lateral extraction of sealing box with dismantling tool
- 5 Sealing box ready to be replaced



Our references:

Altuglas, Arkema, Givaudan, Sanofi, Solvay, Technip, Total...