

JET[®]


**HIGH TECHNOLOGY AGITATOR
FOR STRATEGICAL PROCESSES**

- AGITATION FOR INTENSIVE USE AND HARD WORKING ENVIRONMENT: PRESSURE, TEMPERATURE, PRODUCT
- EQUIPPED WITH THE MOST ADVANCED SEALING SYSTEMS TECHNOLOGIES
- ERGONOMICS FOR FAST MAINTENANCE OPERATIONS

Agitator with JET[®] Type turret,
dedicated to chemical, pharmaceutical
and petrochemical processes

Up to 180 bars, 200 kW and 300°C

- > Chemical reaction
- > Heat transfer
- > Crystallization
- > Fermentation








ATEX
ISO 9001


mixel
agitators

- **Guiding turret** for lateral extraction of sealing box
- Sealing box maintenance **with full tank**
- **Fast dismantling** of the sealing box within less than 4 hours
- **Easy access** to sealing box
- Hydraulic jack for **highly secured dismantling operation**
- **Only one technician** to operate maintenance in safe conditions
- **No need of extra specific tool**

► Sealing system dismantling stages with full or empty tank



- 1 1st dismantling stage
- 2 Uncoupling of driving shaft
- 3 Uncoupled and blocked driving shaft
- 4 Lateral extraction of sealing box with dismantling tool
- 5 Sealing box ready to be replaced



Our references:
Altuglas, Arkema, Givaudan, Sanofi, Solvay, Technip, Total...